



SCOPE OF ACCREDITATION TO ISO/IEC 17025:2005

ENDRESS+HAUSER CANADA LTD.
 1075 Sutton Drive
 Burlington, Ontario, CANADA L7L 5Z8
 Mickala Hohmann (Quality Manager) Phone: 905 681 4265
 Mike Miller (Calibration Manager) Phone: 905 630 1085

CALIBRATION

Valid To: June 30, 2018

Certificate Number: 3597.01

In recognition of the successful completion of the A2LA evaluation process, accreditation is granted to this laboratory to perform the following calibrations¹:

I. Fluid Quantities

Parameter/Equipment	Range	CMC ^{2,4} (±)	Comments
Liquid Flow (Water) – Flowmeter ³ :			
Mass Flowrate	Up to 650 kg/min	0.11 %	Portable flow rig with Coriolis master meters 83F08, 83F25, 83F50
Volumetric Flowrate	Up to 650 l/min	0.14 %	
Mass Flowrate (Current)	Up to 650 kg/min	0.16 %	
Volumetric Flowrate (Current)	Up to 650 l/min	0.18 %	

II. Mechanical

Parameter/Equipment	Range	CMC ² (±)	Comments
Vacuum/Pressure ³ – Gauges and Transducers			
Pneumatic, Gauge Pressure	(-160 to 160) inH ₂ O (-15 to 30) psig (-15 to 300) psig	0.12 inH ₂ O 0.010 psig 0.11 psig	Beamex MC6 field calibrator, pneumatic pressure source.

III. Thermodynamic

Parameter/Equipment	Range	CMC ² (±)	Comments
Temperature ³ – RTD Thermometers	(-15 to 110) °C (50 to 350) °C	0.16 °C 0.16 °C	Beamex MC6 Field Calibrator, Fluke Dry- Block and precision RTD temperature probe

¹ This laboratory offers commercial calibration and field calibration services, where noted.

² Calibration and Measurement Capability Uncertainty (CMC) is the smallest uncertainty of measurement that a laboratory can achieve within its scope of accreditation when performing more or less routine calibrations of nearly ideal measurement standards or nearly ideal measuring equipment. CMCs represent expanded uncertainties expressed at approximately the 95 % level of confidence, usually using a coverage factor of $k = 2$. The actual measurement uncertainty of a specific calibration performed by the laboratory may be greater than the CMC due to the behavior of the customer's device and to influences from the circumstances of the specific calibration.

³ Field calibration service is available for this calibration and this laboratory meets A2LA R104 – *General Requirements: Accreditation of Field Testing and Field Calibration Laboratories* for these calibrations. Please note the actual measurement uncertainties achievable on a customer's site can normally be expected to be larger than the CMC found on the A2LA Scope. Allowance must be made for aspects such as the environment at the place of calibration and for other possible adverse effects such as those caused by transportation of the calibration equipment. The usual allowance for the actual uncertainty introduced by the item being calibrated, (e.g. resolution) must also be considered and this, on its own, could result in the actual measurement uncertainty achievable on a customer's site being larger than the CMC.

⁴ In the statement of CMC, the value is defined as the percentage of reading, unless otherwise noted.



Accredited Laboratory

A2LA has accredited

ENDRESS+HAUSER CANADA LTD.

Burlington, Ontario, CANADA

for technical competence in the field of

Calibration

This laboratory is accredited in accordance with the recognized International Standard ISO/IEC 17025:2005 *General requirements for the competence of testing and calibration laboratories*. This laboratory also meets any additional program requirements in the field of calibration. This accreditation demonstrates technical competence for a defined scope and the operation of a laboratory quality management system (refer to joint ISO-ILAC-IAF Communiqué dated 8 January 2009).



Presented this 22nd day of July 2016.

A handwritten signature in blue ink, reading "Jim C. Bunt".

Senior Director of Quality and Communications
For the Accreditation Council
Certificate Number 3597.01
Valid to June 30, 2018

For the calibrations to which this accreditation applies, please refer to the laboratory's Calibration Scope of Accreditation.